

X-SERIES PRODUCT RANGE



CMX_γ Analyser

Continuous real time XRD mineralogical analysis for cement blends control



- Large, highly representative sample intake
- Continuous analysis of all minerals of interest (including gypsum in all dehydration states, limestone, flyash, slag etc)
- Proprietary high-resolution, solid state detector for high speed XRD analysis
- Designed for outdoor continuous online operation
- Intuitive and easy to use, with Windows 10 touchscreen user interface and inbuilt camera
- Powered by ClassX software suite
- CMX_β option for combined XRD and XRF analysis
- Smart automated process with incorporated smart hopper and sample preparation robotics

CEMENT OPERATIONS SAVINGS – CMX GAMMA

- ☐ SO_3 is closer to target with more consistent setting times
- ☐ Increase limestone addition closer to target (saving clinker and lowering production cost)
- ☐ More consistent fly ash/ slag control
- ☐ Faster product changeovers
- ☐ Less fringe material
- ☐ Produce more uniform and higher quality product
- ☐ Back-up capability for lab equipment

